# Bellows-Sealed Metering Valves





# **BM** Series

- Micrometer handle for precise, repeatable flow settings
- Working pressures up to 700 psig (48.2 bar)
- Temperatures up to 900°F (482°C)
- 316 stainless steel construction



#### **Features**

- Flow coefficients:
  - 0.019 with metering stem tip
  - 0.30 with regulating stem tip
- Micrometer handles measure stem position in 0.001 in. (0.025 mm) increments.
- Valves open to maximum flow in six turns.
- Slotted handle tops enable adjustments with a screwdriver.
- Panel and bottom mounting are standard.
- Swagelok® tube fitting, tube socket weld, tube butt weld, and Swagelok VCR® fitting end connections are available.

# Handle dead stop protects Stainless steel actuator is needle tip from damage by hardened for strength and overtightening wear resistance Actuator backstop Actuator threads are protected enhances bellows life from system contaminants Ball and double-pin design ensures positive Lock screw locks stem retraction in flow settings<sup>1</sup> Precision-formed Gasket body-tometal bellows provides bellows seal shown; reliable service welded seal available Metering stem tip shown;

feature is used.


regulating stem tip available

① Multiple adjustments may be required for desired flow rate when the lock

# **Technical Data**

Body-to- Bellows Seal	Stem Tip	Stem Taper	C <sub>v</sub>	Internal Volume in.3 (cm3)	Series
Gasket	Metering	3°	0.019	0.07 (1.1)	BMG
Gasket	Regulating	20°	0.30	0.11 (1.6)	BMRG
Welded	Metering	3°	0.019	0.07 (1.1)	BMW
	Regulating	20°	0.30	0.11 (1.6)	BMRW

## **Materials of Construction**



	Component	Series	Material Grade/ASTM Specification
1	Handle	A.II	Silver-mist chrome-plated 303 SS/A582
	Set screw	All	Alloy steel/ANSI 18.3
2	Bushing	All	303 SS/A582
	Set screw	All	Alloy steel/ANSI 18.3
3	Barrel	All	Silver-mist chrome-plated 303 SS/A582
	Set screw	All	Alloy steel/ANSI 18.3
4	Panel mount nut	All	316 SS/B783
5	Bonnet nut	All	Silver-plated 316 SS/A479
6	Bonnet	All	316 SS/A479
	Lock screw	All	Alloy steel/ANSI 18.3
7	Actuator	All	416 SS/A582
	Actuator pins	All	420 SS/A276
8	Bearing	All	420C SS
9	Stem		316 SS/A479
	Bellows	All	321 SS/A269
	Weld ring		316 SS/A479
10	Stem adapter	BMRG, BMRW	316 SS/A479
11	Stem tip	All	Hard chrome-plated 316 SS/A479
12	Gasket	BMG, BMRG	Silver-plated 316 SS/A580
13	Body	All	316 SS/A479
	Lubricants	All	Molybdenum disulfide-based dry film and paste

Wetted components listed in italics.



## **Pressure-Temperature Ratings**

Material	316 SS			
Series	BMW, BMRW	BMG, BMRG		
Temperature, °F (°C)	Working Pressure, psig (bar)			
-20 (-28) to 100 (37) 200 (93) 300 (148) 400 (204)	700 (48.2) 610 (42.0) 530 (36.5) 450 (31.0)	700 (48.2) 610 (42.0) 530 (36.5) 450 (31.0)		
500 (260) 600 (315) 650 (343) 700 (371)	375 (25.8) 300 (20.6) 260 (17.9) 230 (15.8)	375 (25.8) 300 (20.6) —		
750 (398) 800 (426) 850 (454) 900 (482)	200 (13.7) 160 (11.0) 130 (8.9) 100 (6.8)	- - - -		

## **Handle Temperature Gradient**

When Valve Seat Is	Valve Handle Is
600°F (315°C)	250°F (121°C)
900°F (482°C)	325°F (162°C)

### **Testing**

Every BM series metering valve is helium leak tested to a maximum leak rate of  $4 \times 10^{-9}$  std cm<sup>3</sup>/s at the envelope and body seal.

## Cleaning and Packaging

Swagelok BM series metering valves with VCR end connections are processed in accordance with Swagelok Special Cleaning and Packaging (SC-11) catalog, MS-06-63, to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C.

Swagelok BM series metering valves with other end connections are processed in accordance with Swagelok Standard Cleaning and Packaging (SC-10) catalog, MS-06-62; special cleaning and packaging are available as an option.


## Oxygen Service Hazards

For more information about hazards and risks of oxygenenriched systems, refer to Oxygen System Safety technical report, MS-06-13.


# Flow Data at 70°F (20°C)




#### Air



#### Water



#### Flow Coefficient at Turns Open



### **Factory Flow Settings**

#### BMG and BMW Series

With 10 psig (0.68 bar) inlet pressure and the flow rate from 10 to 15 cm<sup>3</sup>/min, the handle is set at 0. BMG and BMW series valves are not intended for shutoff service.

#### BMRG and BMRW Series

Following a helium leak test of the valve seat to a maximum leak rate of  $7 \times 10^{-7}$  std cm<sup>3</sup>/s, the handle is set at 0. BMRW series valves are not recommended for shutoff above 600°F (315°C).




⚠ To increase service life, ensure proper valve performance, and prevent leakage, apply only as much torque as is required to achieve positive shutoff in valves rated for shutoff service.



# **Ordering Information and Dimensions**

Select an ordering number.

Dimensions, in inches (millimeters), are for reference only and are subject to change.



End Connections			Ordering	Dimensions, in. (mm)				
Туре	Size	Series	Number	Orifice	Α	В	С	D
Fractional	1/4 in.	BMG	SS-4BMG	0.057 (1.4)	5.24 (133)	1.45 (36.8)	0.56 (14.2)	1.06 (26.9)
		BMRG	SS-4BMRG	0.166 (4.2)	5.22 (133)			
Swagelok tube fitting		BMW	SS-4BMW	0.057 (1.4)	5.17 (131)	1.42 (36.1)		
		BMRW	SS-4BMRW	0.166 (4.2)	5.15 (131)			
	6 mm	BMG	SS-6BMG-MM	0.057 (1.4)	5.24 (133)	1.45 (36.8)	0.56 (14.2)	1.06 (26.9)
Metric		BMRG	SS-6BMRG-MM	0.166 (4.2)	5.22 (133)			
Swagelok tube fitting		BMW	SS-6BMW-MM	0.057 (1.4)	5.17 (131)	1.42 (36.1)		
		BMRW	SS-6BMRW-MM	0.166 (4.2)	5.15 (131)			
	1/4 in. and 3/8 in.	BMG	SS-4BMG-TW	0.057 (1.4)	5.24 (133)	1.45 (36.8) 1.42 (36.1)	0.56 (14.2)	1.00 (25.4)
Tube socket and tube		BMRG	SS-4BMRG-TW	0.166 (4.2)	5.22 (133)			
butt weld		BMW	SS-4BMW-TW	0.057 (1.4)	5.17 (131)			
		BMRW	SS-4BMRW-TW	0.166 (4.2)	5.15 (131)			
	1/4 in	BMG	SS-4BMG-VCR	0.057 (1.4)	5.24 (133)	1.45 (36.8)	0.44 (11.2)	1.00 (25.4)
Integral male VCR		BMRG	SS-4BMRG-VCR	0.166 (4.2)	5.22 (133)			
fitting		BMW	SS-4BMW-VCR	0.057 (1.4)	5.17 (131)	1.42		
		BMRW	SS-4BMRW-VCR	0.166 (4.2)	5.15 (131)	(36.1)		

Dimensions shown with Swagelok tube fitting nuts finger-tight.

# Special Cleaning and Packaging (SC-11)

Swagelok BM series metering valves with VCR end connections are processed in accordance with Swagelok *Special Cleaning and Packaging (SC-11)* catalog, MS-06-63, to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C.

To order special cleaning and packaging for BM series valves with other end connections, add **-SC11** to the valve ordering number.

Example: SS-4BMG-SC11

# Welded Female VCR Face Seal Fittings

- Factory welded to valves with tube butt weld end connections
- 316 SS fittings on stainless steel valves

To order, add a designator to the ordering number for a valve with fractional Swagelok tube fitting end connections.

Fitting Size	Designator	Overall Length in. (mm)			
1/4 in.	-V51	2.76 (70.1)			
1/2 in.	-V16	4.60 (117)			

Example: SS-4BMG-V51

#### Special Alloys

Many BM series valves are available in brass and alloy 400 materials. BMW and BMRW series valves are not available in brass. Contact your authorized Swagelok sales and service representative for more information.

# **Maintenance Kits**

Bellows, stem tip/adapter, and gasket kits are available for BMG and BMRG series valves. See the Swagelok *Bellows-Sealed Valve Maintenance Kits* catalog, MS-02-66.

Caution: Do not mix or interchange parts with those of other manufacturers.



#### Introduction

Since 1947, Swagelok has designed, developed, and manufactured high-quality, general-purpose and specialty fluid system products to meet the evolving needs of global industries. Our focus is on understanding our customers' needs, finding timely solutions, and adding value with our products and services.

We are pleased to provide this global edition of the book-bound *Swagelok Product Catalog*, which compiles more than 100 separate product catalogs, technical bulletins, and reference documents into one convenient, easy-to-use volume. Each product catalog is up to date at the time of printing, with its revision number shown on the last page of the individual catalog. Subsequent revisions will supersede the printed version and will be posted on the Swagelok website and in the Swagelok electronic Desktop Technical Reference (eDTR) tool.

For more information, visit your Swagelok website or contact your authorized Swagelok sales and service representative.

### **Warranty Information**

Swagelok products are backed by The Swagelok Limited Lifetime Warranty. For a copy, visit swagelok.com or contact your authorized Swagelok representative.

#### Safe Product Selection

When selecting a product, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

Caution: Do not mix or interchange parts with those of other manufacturers.

Not all trademarks listed below apply to this catalog. Swagelok, Ferrule-Pak, Goop, Hinging-Collecting, IGC, Kenmac, Micro-Fit, Nupro, Snoop, Sno-Trik, SWAK, VCO, VCR, Ultra-Torr, Whitey-TM Swagelok Company 15-7 PH—TM AK Steel Corp. AccuTrak, Beacon, Westlock-TM Tyco International Services Aflas-TM Asahi Glass Co., Ltd. ASCO, El-O-Matic—TM Emerson AutoCAD-TM Autodesk, Inc. CSA-TM Canadian Standards Association Crastin, DuPont, Kalrez, Krytox, Teflon, Viton-TM E.I. duPont Nemours and Company DeviceNet-TM ODVA Dyneon, Elgiloy, TFM—TM Dyneon Elgiloy—TM Elgiloy Specialty Metals FM—TM FM Global Grafoil-TM GrafTech International Holdings, Inc. Honeywell, MICRO SWITCH—TM Honeywell MAC—TM MAC Valves Microsoft, Windows-TM Microsoft Corp. NACE—TM NACE International PH 15-7 Mo, 17-7 PH—TM AK Steel Corp picofast-Hans Turck KG Pillar—TM Nippon Pillar Packing Company, Ltd. Raychem—TM Tyco Electronics Corp. Sandvik, SAF 2507—TM Sandvik AB Simriz-TM Freudenberg-NOK SolidWorks—TM SolidWorks Corporation UL—Underwriters Laboratories Inc. Xvlan-TM Whitford Corporation © 2019 Swagelok Company